

ProForce® 1200XP HEPA
ProForce® 1500XP HEPA

107251 ProForce 1200XP HEPA **\$459**
 107252 ProForce 1500XP HEPA **\$569**

Our top-of-the-line ProForce uprights have evolved into superior cleaning machines. The ProForce 15" uprights provide exceptional cleaning in a high-filtration upright to improve reach, durability, and Indoor Air Quality. The dual motor system and HEPA exhaust filter maximize efficiency and effectiveness. The powerful ProForce contains a high-performance dual-motor system and a low profile, L-shaped head perfect for vacuuming under and around furniture. ProForce 1500XP HEPA and ProForce 1200XP HEPA models are equipped with premium quality on-board tools including a lightweight plastic wand with a super stretch-hose.

The ProForce 1200XP HEPA is designed for advanced versatility allowing the 12" powerhead to reach even smaller spaces.



HIGH PILE



SUSTAINABLE



COST OF OWNERSHIP



INDOOR AIR QUALITY



LAYS FLAT

Specifications

Weight:	18 lbs./8.17 kg
Airflow:	96 CFM
Static Lift:	84 in.
Motor:	924 W Dual Motor/10 A
Decibel:	67 dBA
Capacity:	3.25 qt/3 L
Four Level Filtration w/ HEPA:	522 sq. in. total media

Warranty

3 years parts , labor, motor and molded body parts (except for wear items)