



# PROTEAM VACUUMING PRODUCTIVITY *Guide\**

SQUARE METERS	DUAL MOTOR (301.285 m2 per Hour)	HIGH EFFICIENCY SPEED CANISTER VACUUM (634.156 m2 per Hour)	BACKPACK VACUUM (688.13 m2 per Hour)	BACKPACK VACUUM* (929.03 m2 per Hour)	BACKPACK CORDLESS** (983.09 m2 per Hour)	BACKPACK CORDLESS*** (1327.21 m2 per Hour)
<b>9,290</b>	30.84 hours	14.65 hours	13.50 hours	10.00 hours	<b>9.45 hours</b>	<b>7 hours</b>
<b>8,826</b>	29.29 hours	13.46 hours	12.83 hours	9.50 hours	<b>8.98 hours</b>	<b>6.65 hours</b>
<b>8,361</b>	27.75 hours	12.75 hours	12.15 hours	9.00 hours	<b>8.51 hours</b>	<b>6.30 hours</b>
<b>7,897</b>	26.21 hours	12.04 hours	11.48 hours	8.50 hours	<b>8.03 hours</b>	<b>5.95 hours</b>
<b>7,432</b>	24.67 hours	11.33 hours	10.80 hours	8.00 hours	<b>7.56 hours</b>	<b>5.60 hours</b>
<b>6,968</b>	23.13 hours	10.62 hours	10.13 hours	7.50 hours	<b>7.09 hours</b>	<b>5.25 hours</b>
<b>6,503</b>	21.58 hours	9.92 hours	9.45 hours	7.00 hours	<b>6.62 hours</b>	<b>4.90 hours</b>
<b>6,039</b>	20.04 hours	9.21 hours	8.78 hours	6.50 hours	<b>6.14 hours</b>	<b>4.55 hours</b>
<b>5,574</b>	18.50 hours	8.50 hours	8.10 hours	6.00 hours	<b>5.67 hours</b>	<b>4.2 hours</b>
<b>5,110</b>	16.96 hours	7.79 hours	7.43 hours	5.50 hours	<b>5.20 hours</b>	<b>3.85 hours</b>
<b>4,645</b>	15.42 hours	7.08 hours	6.75 hours	5.00 hours	<b>4.73 hours</b>	<b>3.5 hours</b>
<b>4,181</b>	13.88 hours	6.37 hours	6.08 hours	4.50 hours	<b>4.25 hours</b>	<b>3.15 hours</b>
<b>3,716</b>	12.33 hours	5.67 hours	5.40 hours	4.00 hours	<b>3.78 hours</b>	<b>2.8 hours</b>
<b>3,252</b>	10.79 hours	4.96 hours	4.73 hours	3.50 hours	<b>3.31 hours</b>	<b>2.45 hours</b>
<b>2,784</b>	9.25 hours	4.25 hours	4.05 hours	3.00 hours	<b>2.84 hours</b>	<b>2.1 hours</b>
<b>2,323</b>	7.71 hours	3.66 hours	3.38 hours	2.50 hours	<b>2.36 hours</b>	<b>1.75 hours</b>
<b>1,858</b>	6.17 hours	2.83 hours	2.70 hours	2.00 hours	<b>1.89 hours</b>	<b>1.4 hours</b>
<b>1,394</b>	4.63 hours	2.12 hours	2.03 hours	1.50 hours	<b>1.42 hours</b>	<b>1.05 hours</b>
<b>929</b>	3.08 hours	1.46 hours	1.35 hours	1.00 Hour	<b>56.70 minutes</b>	<b>42 minutes</b>
<b>465</b>	1.54 hours	43.95 minutes	40.50 minutes	30.00 minutes	<b>28.35 minutes</b>	<b>21 minutes</b>
<b>232</b>	46.25 minutes	21.97 minutes	20.25 minutes	15.00 minutes	<b>14.18 minutes</b>	<b>10.5 minutes</b>
<b>93</b>	18.50 minutes	8.79 minutes	8.10 minutes	6.00 minutes	<b>5.67 minutes</b>	<b>4.2 minutes</b>
Compared to:	Competitive Single Motor Upright (265.424 m2 per hour)	Competitive Tank Canister (232.258 m2 per hour)		*Used in a Team Cleaning System	** Based on recent field tests	***Used in a Team Cleaning System based on recent field tests

Sources— ISSA 612 Cleaning Times (www.issa.com). Used with permission.

8100 West Florissant Avenue, Building T • St. Louis, MO 63136 • 866.888.2168 • 800.541.1456  
 customerservice.proteam@emerson.com • proteam.emerson.com

#500004 Rev. 1/2017

