

SUPER HALFVAC™
PROTEAM BID SPECIFICATIONS
HIPSTYLE VACUUM CLEANER

BODY COMPOSITION – BAG HOUSING, MOTOR HOUSING, FILTER DOOR	Rotational molded, High-density Linear Polyethylene Vacuum motor housing and Exhaust filter door made from high impact Poly Carbonate
BODY DIMENSIONS	12" H x 8" W x 13" L
CAP	Injection molded caps snaps onto bag housing --does not require any latches, hinges, or additional hardware.
WEIGHT	9.8 lbs.
FILTRATION	High Efficiency 5-level Filtration (1515 sq. in.) to include: 1. Reusable Intercept Micro Filter @ 496 inches of filtration media 2. SEMS Cloth filter with Integrated Rubber Vac Seal 3. Dome filter with replaceable media filter (covering motor) 4. First Stage HEPA Filtration exhaust air diffuser 5. Second Stage HEPA Filtration exhaust air diffuser
SOUND LEVEL	68 dB
MOTOR	One-stage, single speed, thru-flow, over mounted at the top of the bag housing. 1056 Watts 8.8 Amps 106" Water lift 111 CFM Airflow 50-60 Hz, 120 Volts Auto Resetable Discrete Thermal Switch for motor Overtemp protection
EXHAUST AIR	Torturous path baffling and air foil exhaust
BACKPACK/WAIST BELT ASSEMBLY	Adjustable shoulder and sternum strap system and padded waist belt. Versatile waist belt design allows the user to decide the most comfortable position with multiple wearing options.
POWER CORD	Detachable 50 foot extension cord, 16/3 gauge with molded plug which attaches to the 14/3 gauge vacuum pig tail cord with exclusive molded strain relief. Schulte Cord Management System
POWER SWITCH	Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.
VACUUM HOSE	1 1/2" diameter, 18" 3 to 1 stretch hose
CAPACITY	6 quart filter capacity

SUPER HALFVAC™
PROTEAM BID SPECIFICATIONS
HIPSTYLE VACUUM CLEANER
Page II

COMMON ATTACHMENTS	1. Two piece 56" Aluminum Two-Bend wand, w/button lock, 1 1/2" in diameter 2. 14" E-Z Glide® floor tool(w/ replacable brush) – for carpet or hard surface floors 3. 3" plastic vacuum dust brush 4. 5" plastic upholstery tool 5. 17" plastic crevice tool *Many other attachments available for specific needs.
ORIGIN	Manufactured and assembled in USA
WARRANTY	3 years on Parts, Labor and Motor - (except for wear and tear items) Molded body – 3 years
CERTIFICATION	Fully certified by TUV/NRTL to UL 1017. Certified in the United States and Canada (equivalent to UL certification). CSA-C22.2 no 243-01 CRI Silver Seal of Approval Certification

April 6, 2010 Rev D