

ProGuard® 15/20
PROTEAM BID SPECIFICATIONS
WET/DRY VACUUM CLEANER

| | |
|---------------------------|---|
| BODY COMPOSITION | Polypropylene Motor cover, collector and HDPE tank. |
| BODY DIMENSIONS | 39.9"L" X, 29.2"W X 41"H |
| CASTERS/WHEELS | Patent Pending Unique variable wheel pattern for increased maneuverability. 2-10" Wheels, 2 – 4" Casters |
| WEIGHT | 215 Gallon – 68 lbs (31 kg), 20 Gallon – 70 lbs (32 kg) |
| FILTRATION | Patent Pending 3 Layer Fine Dust Cartridge, 1276 sq. in. Intercept Micro Filter, Optional Patent Pending Wet Filter, 105 sq. in. (Polypropylene Screen) |
| SOUND LEVEL | 69 dBA |
| MOTOR | Two-Stage By-Pass Motor 95" Water lift 105 CFM Airflow 1380 Watts 9.5 Amps 15A, 120 VAC, 121C rating (Thermodisc) Overtemp motor protection |
| CART SYSTEM | Ergonomic handle system, rear or center wheel position options |
| POWER CORD | 50" 14 AWG with Twist-Lock Pigtail Connection |
| POWER SWITCH | Single pole, single throw, 15A/125VAC rating |
| VACUUM HOSE | 10' Hose, 1 1/2" diameter, secure lock |
| CAPACITY | 15 Gallon (57 liter) or 20 Gallon (76 liter). Includes float mechanism to prevent tank overflow and protect motor from debris and moisture damage. Dual Drain feature tip and pour or drain hose. |
| COMMON ATTACHMENTS | 1. Two piece wand, button-lock, 1 1/2" in diameter 2. Bristle Floor Tool 3. Squeegee Tool 4. Crevice Tool 5. Dust Brush 6. Front Mount Squeegee |
| WARRANTY | 3 year on Parts, Labor and Motor - (except for wear and tear items) Lifetime warranty, Molded body Parts * See owner's manual for complete warranty details |
| CERTIFICATION | This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243) |

3/17/16