

# ProGen® 15

## PROTEAM BID SPECIFICATIONS – UPRIGHT VACUUM CLEANER

|                               |  |
|-------------------------------|--|
| <b>BODY COMPOSITION</b>       | Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS  |
| <b>BODY DIMENSIONS</b>        | 15" wide power nozzle X 46.5 inches high; power nozzle 4.5" high @ 4" deep   |
| <b>CAP</b>                    | Injection molded patent pending cap secured cam lock closure   |
| <b>WEIGHT</b>                 | 18 lbs.  |
| <b>BUMPER PROTECTION</b>      | A soft 1" wide bumper, affixed around the power nozzle for wall and furniture protection   |
| <b>FILTRATION</b>             | 3 Level Filtration w/ HEPA Media Filters<br>Patent Pending Snap Lock Interecept Micro Filter<br><ol style="list-style-type: none"> <li>1. Motor Intake Filter</li> <li>2. (2) Post motor replaceable HEPA Media filters</li> </ol> Earned Seal of Approval from the the Carpet and Rug Institute signifying the vacuum systems meet higher standards for carpet cleaning effectiveness and Indoor Air Quality. Meets the requirements of the US Green Building Council's LEED rating system on performance and filtration. |
| <b>SOUND LEVEL</b>            | 69 dBa w/power nozzle  |
| <b>MOTOR</b>                  | Single Motor<br>9.8 Amps<br>93" Water lift<br>100" CFM Airflow<br>1100 Watts/120 Volts<br>50-60 Hz<br>Automatic thermal shut off switch – safety device<br>Clutch protected dirve system / auto shutoff if brush jams<br>Anti-Slip cogged belt drive for powerhead motor, long life 8mm belt width   |
| <b>EXHAUST AIR</b>            | Displaced by 2 post motor HEPA media filters   |
| <b>POWER CORD</b>             | Patent pending quick change replaceable 50 foot power cord, 18/3 gauge with molded plug which attaches to the vacuum with an exclusive molded plug. Quick release cord wrap.   |
| <b>POWER SWITCH</b>           | Heavy duty rocker type switch mounted in the handle.   |
| <b>VACUUM HOSE</b>            | Anti-Static grounded black hose, stretches to 8 feet long, 1 ½" diameter with wand handle  |
| <b>WHEELS</b>                 | Large rubber 5" wheels for easy maneuverability  |
| <b>CAPACITY</b>               | Top loading, 3.25 qt. filter capacity  |
| <b>ON BOARD TOOLS</b>         | Upholstery Tool & Crevice Tool   |
| <b>MAINTENANCE</b>            | Remove clogs through 4 access points: under the powerhead, at both ends of the hose, where the wand attaches to the base. Brush roll removed without tools.  |
| <b>ANIMATED LIGHT DISPLAY</b> | Alert user of full bag, brush jam and clog issues. LED front lights brighten the cleaning path.  |
| <b>WARRANTY</b>               | 3 year parts, labor, motor and molded body parts – (except for wear items)   |
| <b>CERTIFICATION</b>          | This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)   |