

TailVac®

PROTEAM BID SPECIFICATIONS HIPSTYLE VACUUM CLEANER

BODY COMPOSITION	Rotational molded, high tensile strength, impact resistant, recyclable, memory retaining High-density Linear Polyethylene
BODY DIMENSIONS	12.5" H x 8" W x 15.75" L
CAP	Injection molded twist cap attaches to vac body by twisting onto body, does not require any latches, hinges, or additional hardware
WEIGHT	8.0 lbs
BUMPER PROTECTION	A soft 1 1/8" wide bumper, affixed to bottom of the vacuum for wall and furniture protection
FILTRATION	High Efficiency Four Level filtration (691 sq. in.) to include: 1. Reusable Intercept Micro Filter 2. Micro Cloth Filter with Integrated Rubber Vac Seal 3. Replaceable Dome filter (covering motor) 4. Sound reducing foam and foam air diffuser Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.
SOUND LEVEL	65 dBA
MOTOR	One-stage, single speed, thru-flow, mounted at the bottom of the vacuum body 5.7 Amps 63" Water lift 112 CFM Airflow 684 Watts/120 Volts 50-60 Hz Resetable Discrete Thermal Switch for Overtemp motor protection
EXHAUST AIR	Displaced by Foam Diffuser filter with sound foam
BACKPACK ASSEMBLY	Padded, adjustable strap system and accessory tool loops permanently attached to padded waist belt. Versatile waist belt design allow the user to decide the most comfortable position with multiple wearing options.
POWER CORD	Detachable 50 foot extension cord, 16/3 gauge with molded plug which attaches to the vacuum pig tail cord with exclusive molded on strain relief.
POWER SWITCH	Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.
VACUUM HOSE	1 1/2" diameter or 1 1/4" diameter, 18" 3 to 1 stretch hose
CAPACITY	Top loading, 6 quart filter capacity
COMMON ATTACHMENTS	1. Telescoping Wand or Two Piece Wand 2. 14" Xover® Floor Tool – for carpet or hard surface floors 3. 3" plastic vacuum dust brush 4. 5" plastic upholstery tool 5. 17" plastic crevice tool *Many other attachments available for specific needs.
WARRANTY	Parts, Labor and Motor - 3 year (except for wear and tear items) Molded housing – Lifetime warranty
CERTIFICATION	Certified in the United States and Canada to UL 1017/CSA C22.2 No. 243 by TÜV SÜD America. Certificate number: U8 10 12 62289 016.