

ProBlitz®/ProBlitz XP
PROTEAM BID SPECIFICATIONS
AIR MOVER

| | |
|-------------------------|---|
| BODY COMPOSITION | High-Impact Polypropylene w/built-in Cord Wrap |
| BODY DIMENSIONS | 16.36"Lx12.68Wx18.21H |
| WEIGHT | 28.0 lbs (12.7 kg) |
| SOUND LEVEL | Low: 63 dBA, Medium: 65 dBA, High: 66 dBA |
| MOTOR | Low: 2.5 Amps, Medium: 2.7 Amps, High: 3.0 Amps 2200 CFM Airflow (max) 360 Watts/120 Volts/.4 HP/Capacitor Start 50-60 Hz Automatic Resetting Integral Thermal Switch for Overtemp motor protection |
| BLOWER WHEEL | Calcium carbonate filled Polypropylene |
| POWER CORD | 30 foot extension cord, 18/3 gauge with grounded plug |
| POWER SWITCH | single throw, rotary type switch |
| DRYING POSITION | Three - 0°, 45°/60° (XP only), 90° |
| TRANSPORTATION | Telescoping handle and wheels (XP only) |
| WARRANTY | Parts, Labor and Motor - 3 year Molded housing – Lifetime warranty |
| CERTIFICATION | This products is UL Listed in the US to UL 507 and in Canada to CSA C22.2 No. 113 by UL. Certificate number: 20130218-E229261 |