

ProCare® 15
PROTEAM BID SPECIFICATIONS
UPRIGHT VACUUM CLEANER
2-21-07 Rev B

| | |
|-------------------|---|
| BODY COMPOSITION | Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS & Poly Carbonate |
| BODY DIMENSIONS | 15" wide power nozzle X 48" high |
| WARRANTY | Molded housing - Lifetime warranty Other components - 5 year (except for wear items), Residential use only. 3 Years if used commercially |
| WEIGHT | 17 lbs. |
| BUMPER PROTECTION | A soft 1" wide bumper, affixed around the power nozzle for wall and furniture protection |
| FILTRATION | Four Level Filtration W/HEPA Media 393 sq. in to include: 1. Disposable Intercept Micro Filter @ 248 inches of filtration media 2. Foam Motor Inlet Filter 3. High Efficiency Exhaust Filter |
| SOUND LEVEL | 70 dB w/power nozzle |
| MOTOR | Dual Motor Construction allows one motor to power the brush roll while the other motor powers the vacuum. 11 Amps 84" Water lift 96" CFM Airflow 1320 Watts/120 Volts 50-60 Hz Automatic Thermal Shut Off switch – Saftey Device Anti-Slip cogged belt drive for powerhead motor |
| EXHAUST AIR | Displaced by 2.75" X 3.5" laminated High-efficiency exhaust filter |
| CERTIFICATION | Fully certified by <u>CSA/NRTL</u> . This means that they are certified in the United States (to UL 1017) as well as in Canada. File #LR-80972 |
| POWER CORD | Replacable 35 foot power cord, 18/3 gauge with molded plug which attaches to the vacuum with an exclusive molded plug. Includes quick release cord dump. |
| POWER SWITCH | Ergonomic padded handle grip with conveniently mounted 3-way power switch |
| USER INTERFACE | Electronic System Performance Indicator, alerts user of Bag Full, air flow restriction, or jammed brush roller. |
| CAPACITY | Top loading, 3.25 qt. filter capacity |

