

ProForce® 1200XP HEPA

PROTEAM BID SPECIFICATIONS

UPRIGHT VACUUM CLEANER

BODY COMPOSITION	Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS & Polycarbonate
BODY DIMENSIONS	12" wide power nozzle X 48" high
WEIGHT	18.0 lbs
BUMPER PROTECTION	A soft 1" wide bumper, affixed around the power nozzle for wall and furniture protection
FILTRATION	High Efficiency Four Level filtration w/HEPA (522 sq. in.) to include: 1. Reusable Intercept Micro Filter 2/3. Double Layer Motor Intake Filter 4. HEPA Exhaust Filter Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.
SOUND LEVEL	67 dBA w/power nozzle
MOTOR	Dual Motor Construction allows one motor to power the brush roll while the other motor powers the vacuum. 10 Amps 84" Water lift 96" CFM Airflow 924 Watts/120 Volts 50-60 Hz Automatic Thermal Shut Off switch – Safety Device Anti-Slip cogged belt drive for powerhead motor
EXHAUST AIR	Displaced by 2.75" X 3.5" laminated High-efficiency exhaust filter
POWER CORD	Replaceable 50 foot power cord, 18/3 gauge with molded plug which attaches to the vacuum with an exclusive molded plug.
POWER SWITCH	Heavy duty double-pole rocker type switch mounted in the handle.
ON BOARD TOOLS	Black, 16" L 3-1 stretch hose with wand and on-board upholstery/dust brush combo tool and crevice tool.
CAPACITY	Top loading, 3.25 quart filter capacity
WARRANTY	3 year parts, labor, motor and molded body parts (except for wear items)
CERTIFICATION	This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)

3/17/16