

ProCare® 15XP

PROTEAM BID SPECIFICATIONS
UPRIGHT VACUUM CLEANER
2-21-07 Rev B

BODY COMPOSITION	Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS & Poly Carbonate
BODY DIMENSIONS	15" wide power nozzle X 48" high
WARRANTY	Molded housing - Lifetime warranty Other components - Parts and Labor - 5 year (except for wear items) Residential use only. 3 Years if Used Commercially
WEIGHT	18 lbs
BUMPER PROTECTION	A soft 1" wide bumper, affixed around the power nozzle for wall and furniture protection
FILTRATION	Four Level Filtration W/HEPA Media 393 sq. in. to include: 1. Disposable Intercept Micro Filter @ 248 inches ² of filtration media 2. Foam Motor Inlet Filter 3. High Efficiency Exhaust Filter
SOUND LEVEL	70 dB w/power nozzle
MOTOR	Dual Motor Construction allows one motor to power the brush roll while the other motor powers the vacuum. 11 Amps 84" Water lift 96" CFM Airflow 1320 Watts/120 Volts 50-60 Hz Automatic Thermal Shut Off switch – Safety Device Anti-Slip cogged belt drive for powerhead motor
EXHAUST AIR	Displaced by 2.75" X 3.5" laminated High-efficiency exhaust filter
CERTIFICATION	Fully certified by <u>CSA/NRTL</u> . This means that they are certified in the United States (to UL 1017) as well as in Canada. File #LR-80972
POWER CORD	Replacable 35 foot power cord, 18/3 gauge with molded plug which attaches to the vacuum with an exclusive molded plug. Includes quick release cord dump.
POWER SWITCH, USER INTERFACE	Ergonomic padded handle grip with conveniently mounted 3-way power switch. Electronic System Performance Indicator, alerts user of Bag Full, air flow restriction, or jammed brush roller.
ON BOARD TOOLS	1.5" Suction Hose, Black, 16" L 3-1 stretch hose with wand and on-board upholstery/dust brush combo tool and crevice tool.
CAPACITY	Top loading, 3.25 qt. filter capacity