

**ProGuard® LI 3 Cordless**  
**PROTEAM BID SPECIFICATIONS**  
**BATTERY - WET/DRY VACUUM CLEANER**

<b>BODY COMPOSITION</b>	Polypropylene Motor cover, shroud, motor cradle, battery cover, HDPE tank.
<b>BODY DIMENSIONS</b>	15.5L" X, 8.5"W X 16"H
<b>CARRY HANDLE</b>	Ergonomic large carry handle, designed for convenient portability, protects power switch from accidental start-ups.
<b>WEIGHT</b>	10.5 lbs
<b>BATTERY RECYCLING</b>	RBRC – 1-800-822-8831
<b>FILTRATION</b>	Patent Pending 3 Layer Fine Dust Cartridge, 903 sq. in.
<b>SOUND LEVEL</b>	72 dBA
<b>MOTOR</b>	38" Water lift 60 CFM Airflow 18-Volt Permanent Magnet DC
<b>BLOWER AIR PORT</b>	Integrated, 1 1/2" Hose Connection
<b>BATTERY</b>	18-volt Lithium Ion, Continuous run time Approximately 11 minutes
<b>BATTERY CHARGER</b>	120 Volt, 60 Hz, AC Only, Charge Time Approximately 30 Minutes
<b>POWER SWITCH</b>	Single pole, single throw, 15A/125VAC rating
<b>VACUUM HOSE</b>	2 – 7 foot stretch Hose, 1 1/2" diameter, secure lock
<b>CAPACITY</b>	3 Gallon (11.4 liter) Includes float mechanism to prevent tank overflow and protect motor from debris and moisture damage.
<b>COMMON ATTACHMENTS</b>	1. Crevice Tool 2. Dust Brush 3. Claw Nozzle 4. Battery Charger
<b>WARRANTY</b>	3 year on Parts, Labor - (except for wear and tear items) Lifetime warranty, Molded body Parts 1 Year on Motor, Battery and Charger * See owner's manual for complete warranty details
<b>CERTIFICATION</b>	This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)

3/17/16