

# GoFree Flex Pro 12Ah

PROTEAM BID SPECIFICATIONS  
BATTERY/BACKPACK VACUUM CLEANER

|                              |  |
|------------------------------|--|
| <b>BODY COMPOSITION</b>      | Injection molded, impact modified polypropylene copolymer  |
| <b>BODY DIMENSIONS</b>       | 7-1/8 x 10-1/8, 24" length top to bottom   |
| <b>CAP</b>                   | Injection molded cap attaches to vac body by three die-cast aluminum latches   |
| <b>WEIGHT</b>                | 18 lbs   |
| <b>BUMPER PROTECTION</b>     | Dual shot injection molded bumper absorbs shocks when unit is dropped  |
| <b>PROLEVEL FILTRATION –</b> | <p>Four Levels of Filtration</p> <ol style="list-style-type: none"> <li>1. Reusable Intercept Micro Filter</li> <li>2. Micro Cloth Filter with Integrated Rubber Vac Seal</li> <li>3. Replaceable Dome filter (covering motor)</li> <li>4. 2 Replaceable HEPA Media Filters after the motor</li> </ol> <p>Exceeds industry regulation testing standards set by the Carpet and Rug Institute on performance and filtration.</p> |
| <b>SOUND LEVEL</b>           | 63.7 dBA ASTM F1334-14   |
| <b>MOTOR</b>                 | <p>one stage, single speed, flow-thru, mounted above the battery</p> <p>10 Amps</p> <p>54" Water lift</p> <p>78 CFM Airflow</p> <p>360 Watts/36 Volts DC</p> <p>Self-resetting thermal protector for Overtemp motor protection</p>   |
| <b>BATTERY</b>               | <p>Approximately 75 minutes of continuous run time</p> <p>Battery Type – Lithium Ion</p> <p>Lithium Ion Battery Module automatically shuts down the battery when it is ready to be charged.</p>  |
| <b>CHARGER</b>               | Approximately 2.5-3 hours to full charge time  |
| <b>EXHAUST AIR</b>           | Dispersed through 2 HEPA media filters   |
| <b>BACKPACK ASSEMBLY</b>     | Breathable mesh material with articulating harness, sternum strap system with accessory tool loops permanently attached to padded waist belt (65" length).   |
| <b>POWER SWITCH</b>          | <u>Heavy duty double pole</u> single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.  |
| <b>VACUUM HOSE</b>           | Black, 56" long, 1 1/2" diameter, <u>swivel cuff, and swivel elbow.</u>  |
| <b>CAPACITY</b>              | Top loading, <u>6 quart</u> filter capacity  |
| <b>COMMON ATTACHMENTS</b>    | <ol style="list-style-type: none"> <li>1. Telescoping Wand or Two Piece Wand</li> <li>2. <u>14" Xover<sup>®</sup> Floor Tool</u> – for carpet or hard surface floors</li> <li>3. 3" plastic vacuum dust brush</li> <li>4. 5" plastic upholstery tool</li> <li>5. 17" plastic crevice tool</li> </ol> <p>*Many other attachments available for specific needs.</p>  |
| <b>WARRANTY</b>              | <p>2 years – motor, battery, charger, 3 years on parts and labor. (except for wear and tear items)</p> <p>Molded housing – Lifetime warranty</p> <p>Articulating harness – 3 years (except for wear and tear items)</p>  |
| <b>CERTIFICATION</b>         | This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)   |