

# GoVac™ BP

## PROTEAM BID SPECIFICATIONS BATTERY BACKPACK VACUUM CLEANER

BODY COMPOSITION	Rotational molded, high tensile strength, impact resistant, recyclable, memory retaining High-density Linear Polyethylene
BODY DIMENSIONS	6.5" cylinder, 24" in length top to bottom
CAP	Injection molded twist cap attaches to vac body by twisting onto body, does not require any latches, hinges, or additional hardware
WEIGHT	22.0 lbs
BUMPER PROTECTION	A soft 1.125" wide bumper, affixed to bottom of the vacuum for wall and furniture protection
FILTRATION	High Efficiency Four Level filtration (791 sq. in.) to include: <ol style="list-style-type: none"> <li>1. Reusable Intercept Micro Filter @ 496 inches of filtration media</li> <li>2. SEMS Cloth filter with Integrated Rubber Vac Seal</li> <li>3. Dome filter with replaceable media filter (covering motor)</li> <li>4. Sound reducing foam and foam air diffuser</li> </ol>
SOUND LEVEL	69 dB Vacuum Quietly During Business Hours at Decibel Levels Less Than Normal Conversation
MOTOR and BATTERY CHARGER	One-stage, single speed, thru-flow, mounted at the bottom of the vacuum body 36 VDC 70" Water lift 65 CFM Airflow 50 Minutes of Continuous Run Time 3 Hours to Full Charge Time 2 Hours to 90% Charge Time Resetable Discrete Thermal Switch for Overtemp motor protection
EXHAUST AIR	Displaced by 2.5" thick Foam Diffuser filter with sound foam
BACKPACK ASSEMBLY	Integrated battery back plate carries weight evenly across the hips for maximum comfort and mobility.
BATTERY PACK and CONTROLLER ASSEMBLY	Lithium Ion Battery Module automatically shuts down the battery when it is ready to be charged to prevent loss of suction and performance
POWER SWITCH	<u>Heavy duty double pole rocker type switch mounted in a switch box and conveniently attached with Velcro™ to the left side of waist belt. Switch cord is 14/4 gauge with exclusive molded on strain relief.</u>
VACUUM HOSE	<u>Black, 54" long, 1.25" diameter, static dissipating, swivel cuff, and swivel elbow.</u>
CAPACITY	Mid-size Capacity is ideal for cleaning in and around crowded constraints, in stairwells and elevators, Top loading, <u>6 quart</u> capacity filter bag.

# GoVac™ BP

## PROTEAM BID SPECIFICATIONS BATTERY BACKPACK VACUUM CLEANER

Page II

COMMON ATTACHMENTS	<ol style="list-style-type: none"> <li>1. 24” – 40” Chrome Telescoping Wand with button lock, 1.25” in diameter</li> <li>2. <u>10" combination floor tool (w/ replaceable brush)</u> – for carpet or hard surface floors</li> <li>3. 2.5” Rectangular Dust Brush with 90/180 swivel</li> <li>4. 5.5” plastic upholstery tool</li> <li>5. 1.25” x 13" plastic crevice tool</li> <li>6. Adapter, Cuff, 1.25” X 1.25” plastic</li> <li>7. 13” Curved Chrome Wand with button lock and bleeder for electrified hose, 1.25” in diameter</li> </ol>
ORIGIN	Manufactured and assembled in Boise, ID, USA
WARRANTY	<p>1 year prorated on batteries, 1 year on battery charger, 3 years on motor, Lifetime warranty on molded vacuum body</p> <p><u>Santoprene™ backplate – Lifetime warranty (excludes harness assembly)</u></p>
CERTIFICATION	CRI Carpet and Rug Institute Seal of Approval

### PROTEAM UNIQUE FEATURES

OPTIONAL ADDITIONS	<p>Ergonomic Wand Handles</p> <p>Filter Guard (prolongs life of the Intercept Micro Filters)</p> <p>High Filtration Dome Filter Disks</p>
EDUCATIONAL MATERIALS	<p>Backpack Vacuum training video, The ProTeam Way &amp; Set-Up/ Training/Operation DVD</p> <p>School training video – Vacuuming in the Educational Environment</p> <p>Team Cleaning Videos:</p> <ul style="list-style-type: none"> <li>Team Cleaning Over View</li> <li>Vacuum Specialist</li> <li>Restroom Specialist</li> <li>Light Duty Specialist</li> </ul>

Rev A December 19,