

LineVacer® HEPA and ULPA

PROTEAM BID SPECIFICATIONS

BACKPACK VACUUM CLEANER

BODY COMPOSITION	Blow molded, high tensile strength, impact resistant, recyclable, memory retaining High-density Linear Polyethylene
BODY DIMENSIONS	8.5" cylinder, 27" in length top to bottom
CAP	Rotation molded latch cap on top and bottom--safety locks on bottom HEPA/ULPA cap
WEIGHT	13.0 lbs
FILTRATION	Four Level HEPA 99.97% @ .3 Micron Filtration to include (2283 sq. in. total area), Four Level ULPA 99.999% @ .12 Micron Filtration to include (3232 sq. in. total area): 1. Reusable Intercept Micro Filter 2. Micro Cloth Filter with Integrated Rubber Vac Seal 3. Replaceable Dome filter (covering motor) 4. HEPA/ULPA filtered exhaust Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.
SOUND LEVEL	64 dBA
MOTOR	Two-stage, single speed, thru-flow, mounted at the bottom of the vacuum body 6.2 Amps 75" Water lift 124 CFM Airflow 744 Watts/120 Volts 50-60 Hz Resetable Discrete Thermal Switch for Overtemp motor protection
EXHAUST AIR	HEPA/ULPA filtered exhaust
BACKPACK ASSEMBLY	Ventilated two piece ergonomic unbreakable Santoprene™ frame with padded, adjustable shoulder and sternum strap system with accessory tool loops permanently attached to padded waist belt (54"length).
POWER CORD	Detachable 50 foot extension cord, 16/3 gauge with molded plug which attaches to the vacuum pig tail cord with exclusive molded on strain relief.
POWER SWITCH	Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.
VACUUM HOSE	Black, 56" long, 1 1/2" diameter, swivel cuff, and swivel elbow.
CAPACITY	Top loading, 10 quart filter capacity
COMMON ATTACHMENTS	1. Telescoping Wand or Two Piece Wand 2. 14" Xover® Floor Tool – for carpet or hard surface floors 3. 3" plastic vacuum dust brush 4. 5" plastic upholstery tool 5. 17" plastic crevice tool *Many other attachments available for specific needs.
WARRANTY	Parts, Labor and Motor - 3 year (except for wear and tear items) Molded housing – Lifetime warranty
CERTIFICATION	Certified in the United States and Canada to UL 1017/CSA C22.2 No. 243 by TÜV SÜD America. Certificate number: U8 10 12 62289 016. Meets the EPA's definition of a HEPA vacuum and is appropriate for lead paint renovations under the RRP Rule.