

ProGuard® 4 Portable
PROTEAM BID SPECIFICATIONS
WET/DRY VACUUM CLEANER

BODY COMPOSITION	Polypropylene Motor cover, collector and tank.
BODY DIMENSIONS	16L" X, 14"W X 18"H
CASTERS	4 – 2" swivel casters
WEIGHT	12 lbs (5.5 kg)
FILTRATION	Patent Pending 3 Layer Fine Dust Cartridge, 903 sq. in. Intercept Micro Filter, Optional, 814 sq. in.
SOUND LEVEL	76 dBA
MOTOR	One-stage, by-pass motor 9 Amps 51" Water lift 142 CFM Airflow 1080 Watts/120 Volts 50-60 Hz 15A, 120 VAC, 121C rating (Thermodisc) Overtemp motor protection
BLOWER AIR PORT	Integrated, 1 1/2" Hose Connection
CARRY HANDLE	Integrated with a large carry handle, designed for convenient portability.
POWER CORD	20 foot, 18 AWG, Double Insulated Plug
POWER SWITCH	Single pole, single throw, 15A/125VAC rating
VACUUM HOSE	10 foot, 1 1/2" diameter, secure lock
CAPACITY	4 Gallon (15.2 liter) Includes float mechanism to prevent tank overflow and protect motor from debris and moisture damage.
COMMON ATTACHMENTS	1. Two piece wand, button-lock, 1 1/2" in diameter 2. Master Floor Tool 3. Carpet Insert 4. Bristle Insert 5. Squeegee Insert 6. Crevice Tool 7. Dust Brush 8. Claw Nozzle
WARRANTY	3 year on Parts, Labor - (except for wear and tear items) Lifetime warranty, Molded body Parts 1 Year on Motor * See owner's manual for complete warranty details
CERTIFICATION	This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)