

# ProForce<sup>®</sup> 1500 HEPA

## PROTEAM BID SPECIFICATIONS UPRIGHT VACUUM CLEANER 3-1-12 Rev A

BODY COMPOSITION	Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS & Polycarbonate
BODY DIMENSIONS	15" wide power nozzle X 48" high
WARRANTY	3 year parts, labor, motor and molded body parts (except for wear items)
WEIGHT	17 lbs.
BUMPER PROTECTION	A soft 1" wide bumper, affixed around the power nozzle for wall and furniture protection
FILTRATION	Four Level Filtration W/HEPA 522 sq. in. to include: 1. Disposable Intercept Micro Filter @ 248 inches <sup>2</sup> of filtration media 2. Double Layer Motor Intake Filter 3. HEPA Exhaust Filter
SOUND LEVEL	67 dB w/power nozzle
MOTOR	Dual Motor Construction allows one motor to power the brush roll while the other motor powers the vacuum. 10 Amps 84" Water lift 96" CFM Airflow 924 Watts/120 Volts 50-60 Hz Automatic Thermal Shut Off switch – Safety Device Anti-Slip cogged belt drive for powerhead motor
EXHAUST AIR	Displaced by 2.75" X 3.5" laminated High-efficiency exhaust filter
CERTIFICATION	Certified in the United States and Canada to UL 1017/CSA C22.2 No. 243 by TÜV SÜD America. Certificate number: U8 10 12 62289 014.
POWER CORD	Replaceable 50 foot power cord, 18/3 gauge with molded plug which attaches to the vacuum with an exclusive molded plug.
POWER SWITCH	Heavy duty double-pole rocker type switch mounted in the handle.
CAPACITY	Top loading, 3.25 qt. filter capacity