

ProGen® 12

PROTEAM BID SPECIFICATIONS – UPRIGHT VACUUM CLEANER

BODY COMPOSITION	Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS
BODY DIMENSIONS	12" wide power nozzle X 46.5 inches high; power nozzle 4.5" high @ 4" deep
CAP	Injection molded patent pending cap secured cam lock closure
WEIGHT	17 lbs.
BUMPER PROTECTION	A soft 1" wide bumper, affixed around the power nozzle for wall and furniture protection
FILTRATION	3 Level Filtration w/ HEPA Media Filters Patent Pending Snap Lock Interecept Micro Filter <ol style="list-style-type: none"> 1. Motor Intake Filter 2. (2) Post motor replaceable HEPA Media filters Earned Seal of Approval from the the Carpet and Rug Institute signifying the vacuum systems meet higher standards for carpet cleaning effectiveness and Indoor Air Quality. Meets the requirements of the US Green Building Council's LEED rating system on performance and filtration.
SOUND LEVEL	69 dBa w/power nozzle
MOTOR	Single Motor 9.8 Amps 93" Water lift 100" CFM Airflow 1100 Watts/120 Volts 50-60 Hz Automatic thermal shut off switch – safety device Clutch protected dirve system / auto shutoff if brush jams Anti-Slip cogged belt drive for powerhead motor, long life 8mm belt width
EXHAUST AIR	Displaced by 2 post motor HEPA media filters
POWER CORD	Patent pending quick change replaceable 40 foot power cord, 18/3 gauge with molded plug which attaches to the vacuum with an exclusive molded plug. Quick release cord wrap.
POWER SWITCH	Heavy duty rocker type switch mounted in the handle.
VACUUM HOSE	Anti-Static grounded black hose, stretches to 8 feet long, 1 ½" diameter with wand handle
WHEELS	Large rubber 3" wheels for easy maneuverability
CAPACITY	Top loading, 3.25 qt. filter capacity
ON BOARD TOOLS	Upholstery Tool & Crevice Tool
MAINTENANCE	Remove clogs through 4 access points: under the powerhead, at both ends of the hose, where the wand attaches to the base. Brush roll removed without tools.
ANIMATED LIGHT DISPLAY	Alert user of full bag, brush jam and clog issues. LED front lights brighten the cleaning path.
WARRANTY	3 year parts, labor, motor and molded body parts – (except for wear items)
CERTIFICATION	This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)