# GoFit® 3 / 6 PH w/Commercial Power Nozzle Tool Kit



The ProTeam GoFit Series is a lineup of vacuums engineered to deliver maximum comfort and productivity. The 3 and 6-quart units offer even more versatility with the commercial power nozzle tool kit which is a favorite among residential cleaners. The kit comes with the essential tools necessary to make residential cleaning a simpler task including a power nozzle, a two-piece wand, an electrified hose with an elbow cuff and several floor tools.



### Customizable Fit —

four-step quick-adjust FlexFit® harness provides new levels of comfort

### New Level of Clean —

features a power nozzle hook-up on the switchbox

### Cord Management —

includes an improved switchbox which offers an integrated cord wrap design for the unit's 50' power cord

### Easy to Navigate —

maneuver quickly around furniture, tight spaces and other obstacles with the help of the vacuum's reduced profile

### Advanced Filtration —

four levels of filters reducing allergens and asthma triggers

## Join The Movement

### **Specifications**

| Model | Product<br>Weight       | Airflow<br>(CFM) | Static<br>Lift - in. | Motor              | Decibel -<br>dBa | Capacity      | Extension<br>Cord | Filtration*   | Dimensions                    | Hose<br>Length | Warranty**  |
|-------|-------------------------|------------------|----------------------|--------------------|------------------|---------------|-------------------|---|-------------------------------|----------------|---|
| 3 qt  | 11.4 lbs. /<br>5.17 kg. | 153 CFM          | 91 in.               | 1330 W /<br>11.7 A | 68 dBa           | 3 qt. / 3.3 L | 50'               | ProLevel Filtration System with<br>HEPA Media captures 99.79% at<br>0.35 microns per ASTM F3150 | 8.13" x<br>11.94" x<br>14.93" | 48"            | 3 years parts, labor and motor on vacuum, limited lifetime on molded body parts |
| 6 qt  | 12 lbs. /<br>5.44 kg    | 153 CFM          | 91 in.               | 1330 W /<br>11.7 A | 67.9 dBa         | 6 qt. / 6.6 L | 50'               | ProLevel Filtration System with<br>HEPA Media captures 99.82% at<br>0.35 microns per ASTM F3150 | 8.13" x<br>11.94" x<br>18.35" | 48"            | 3 years parts, labor and motor on vacuum, limited lifetime on molded body parts |

#### PERFORMANCE SPECS BASED ON MOTOR SPECS

\*The filtration value of ProTeam's ProLevel Filtration System in this vacuum is achieved by the use of a multi-stage filtration system, including intercept micro filter, micro cloth filter, plastic cage with foam filter, and post-motor filter made from HEPA media, as tested per ASTM F3150.



Experience a fast, efficient and healthy way to clean with the Power Nozzle Tool Kit. Additional benefits include:

### On/off switch -

for cleaning versatility including on med/high pile carpet and then off for hard surfaces

### Low profile —

for vacuuming under and around couches, beds and chairs

### Plus various tools —

that provide ease of use for detailing baseboards, furniture, registers, window seals, ceiling fans and blinds in homes or offices





- 12" Power Nozzle
- Two-Piece Wand w/ Cord Holder
- Electrified Hose w/ Gas Pump Handle
- 2.5" Swivel Dust Brush
- 5.5" Upholstery Tool w/ Removable Brush
- 13" Crevice Tool





- 12" Power Nozzle
- Two-Piece Wand w/ Cord Holder
- Electrified Hose w/ Gas Pump Handle
- 2.5" Swivel Dust Brush
- 5.5" Upholstery Tool w/ Removable Brush
- 13" Crevice Tool



proteam.emerson.com/gofit

866.888.2168

American Lung Association.

NATIONAL PROUD PARTNER

We Support Healthy Air | Lung.org

