

Cleans up to than a corded backpack & than an upright vacuum

Cordless. Comfortable. Efficient.

Introducing our most advanced line of powerful battery-operated backpack vacuums.

Experience comfort and cordless efficiency with the ProTeam GoFit 3 / 6 Cordless Series from the industry leader in innovative backpack vacuum technology. Your team will benefit from the enhanced freedom, comfort and maneuverability to clean in even the hardest-to-reach places. Your business will enjoy greater productivity, operational cost and labor savings, and the ability to take on cleaning challenges in a wide variety of environments.





PERSONALIZE YOUR EXPERIENCE

Choose our new 3-quart size for those with a smaller frame or our best-selling 6-quart size, both free from the constraints of cords and potential tripping hazards.

Clean with cordless efficiency.

Here's why the GoFit 3 / 6 Cordless Series is a more productive, efficient, and comfortable fit for the way you clean.



CUSTOMIZED FIT

Enjoy a personalized/balanced fit with the vacuum's quick-adjust, 4-step, FlexFit® harness system.



EASY-TO-USE POWER SWITCH

A convenient power button located on the side of the unit for easy access and reduction in wear parts.



NOTICEABLY QUIET

Quietly clean around others without disturbing them.

IMPROVED SAFETY

Helps to eliminate tripping and obstacle concerns and is easy to maneuver even in tight spaces.

CONTINUOUS OPERATION

Long-lasting battery power means only two batteries are needed for continuous operation.

EASY MANEUVERABILITY

With a reduced profile/weight balance, these nimble units redefine mobility and go anywhere without the constraints of cords and power outlets.



MULTI-LAYERED PROLEVEL FILTRATION®

The units' three levels of filtration include an Intercept Micro® Filter, Micro Cloth Filter & Dome Filter made with HEPA Media that collects more than 99% of indoor pollutants one micron or larger.



BRUSHLESS MOTOR REDUCES COST OF OWNERSHIP

Powerful and highly efficient without carbon brushes to maintain and produces no carbon dust.



UNINTERRUPTED CORDLESS POWER

Battery charge time is approximately equal to battery runtime, making it convenient to quickly swap batteries from charger to vacuum for continuous cord-free operation.



will change from solid red to flashing green. When charger indicator light changes from flashing green to solid green, battery is 100% charged. Battery Fuel Gauge indicates the approximate runtime remaining on the

battery pack when the display button is

pressed. 4 lights: 80%-100%; 3 lights:

60%-80%; 2 lights: 40%-60%; 1 light:

20%-40%; 1 flashing light: Less than 20%.

RAPID RECHARGE BATTERY TECHNOLOGY

Featuring a 4Ah Lithium-Ion battery for a

lighter-weight quick-cleaning solution, or

the 8Ah Lithium-Ion battery, both with

EASY-TO-READ CHARGE STATUS

Charger indicator light will turn solid red

after inserting battery (standby mode).

When charge cycle begins the indicator

rapid recharge capabilities.

AND BATTERY FUEL GAUGE



SINGLE-LATCH ACCESSIBILITY

Easily change the filter bag with one hand.



SCAN THE CODE AND WATCH THE VIDEO TO **LEARN MORE.**





Experience a 30% increase in productivity.

Productivity remains as one of the top five challenges facility managers face today¹. More than 79% of building service contractors spend over half of their operating budget on labor². Transitioning to cordless vacuuming can dramatically increase an organization's annual labor savings.

Time needed to vacuum 100,000 SQ. FT.



CORDED UPRIGHT

CORDED BACKPACK

ANNUAL SAVINGS \$73,788**



CORDLESS BACKPACK

ANNUAL SAVINGS \$87,688**

*ISSA 612 Cleaning Times **Annual savings based on \$13/hr wage

$^1\,2023$ CMM In-House/Facility Management Benchmarking Survey Report $^2\,2023$ CMM Building Service Contractor Benchmarking Survey Report

GO ANYWHERE

Redefine mobility and go anywhere without the constraints of cords and power outlets.

Go anywhere uninterrupted.

Vacuum more with the GoFit 3 / 6 Cordless Series, which features an all-new energy-efficient motor. And with two battery options designed to be interchangeable with each vacuum model, discover extended runtimes without sacrificing ProTeam's widely recognized high performance.



HIGH / LOW POWER BUTTON

Adjust the speed based on your cleaning challenge for greater power or to extend runtime.

Press once for high when tackling larger cleaning challenges and twice for a lower, daily clean.

Press three to turn off.

Runtime and charge time



4AH

LITHIUM-ION BATTERY

A lighter weight, quick cleaning solution.

On High:

RUNTIME

39 mins*

On Low:

51 mins*

RAPID RECHARGE

Full Charge Time:

61 mins*

LI'

8AH

LITHIUM-ION BATTERY

For larger areas that require a longer runtime.

On High:

83 mins*

On Low:

106 mins*

Full Charge Time:

101 mins*

*Listed times are approximate



Stay comfortable while being more productive.

Our battery-operated backpack vacuums are designed to be as comfortable as they are efficient and productive, utilizing the GoFit harness system.

INCREASED BREATHABILITY

Increases air circulation, reducing warmth and moisture accumulation.



QUICK-ADJUST HARNESS

No tools required - quick adjust system moves upper harness up and down to fit users perfectly.





INTERCHANGEABLE HARNESS

Allows each user to have their own custom-fitted harness.

WIDER AND LONGER LOWER HARNESS

Distributes the weight of the unit for greater comfort.

Our 4-step quick-adjust harness system offers new levels of comfort.

Adaptable to all body frames and numbered with intuitive touchpoints for a custom comfortable fit, this harness is designed to rest comfortably on the user's hips for hours of wear and productivity – all with no tools required.



Adjust the upper harness height for customized balance and fit.



Buckle and adjust the sternum strap, then hit the power and get your clean on.



Adjust the shoulder straps to turn comfort up a notch.



Buckle the waist belt and pull the loose ends for increased weight support.





proteam.emerson.com/gocordless 866.888.2168 customerservice.proteam@emerson.com



Specifications

Model	Product Weight	Airflow (CFM)	Static Lift (in.)	Motor	Decibel (dBA)	Capacity	Battery	Approx. Runtime	Approx. Full Charge Time	Minimum Charge Cycles	Warranty
3 qt	12.8 lbs. / 5.8 kg. (w/ 4Ah) 15.7 lbs. / 7.1 kg. (w/ 8Ah)	65 CFM (low) 70 CFM (high)	55 in. (low) 63 in. (high)	54 VDC 240 W (low) 310 W (high)	63 dBA (low) 66 dBA (high)	3 qt / 3.3 L	Lithium Ion, 4Ah / 8Ah	4Ah Battery: 51 mins. (low) 39 mins. (high) 8Ah Battery: 106 mins. (low) 83 mins. (high)	4Ah Battery: 61 mins. 8Ah Battery: 101 mins.	1000	3 years parts and labor. 2 years motor, battery and charger, limited lifetime on molded body parts
6 qt	13.5 lbs. / 6.1 kg. (w/ 4Ah)	65 CFM (low) 70 CFM (high)	55 in. (low) 63 in. (high)	54 VDC 240 W (low)	65 dBA (low) 67 dBA (high)	6 qt / 6.6 L	Lithium Ion, 4Ah / 8Ah	4Ah Battery: 51 mins. (low)	4Ah Battery: 61 mins.	1000	3 years parts and labor. 2 years motor, battery and charger, limited lifetime
	16.4 lbs. / 7.4 kg. (w/ 8Ah)			310 W (high)				39 mins. (high) 8Ah Battery:	8Ah Battery: 101 mins.		
								106 mins. (low) 83 mins. (high)			on molded body parts









ProTeam is a Proud Partner of the American Lung Association in their fight for clean indoor air.

