

## GoCartVac®

106209\* GoCartVac w/GoCart Kit A (104885)

**\$3,489**

With the ability to plug into a wall socket or run off the large battery reserve, the GoCartVac allows cleaning professionals the ability to clean anywhere, anytime, without the limitations of cords or the concern of noisy equipment. Go anywhere with the GoCartVac's 20' hose.



\*Garbage can not included.



**PRODUCTIVE**



**CORDLESS**



**QUIET**



**INDOOR AIR QUALITY**



**DAY CLEANING**

### Specifications

Airflow:	82 CFM
Static Lift:	67 in.
Motor:	36 V /14.1 A
Decibel:	58 dBA
Capacity:	6 qt/6.6 L
Battery Type:	Sealed (non-spillable), Lead Acid
Approximate Run Time:	1 hour
Approximate Charge Time (w/36V-18.5 amp battery charger):	3.5 hours

### Warranty

6 months on battery
1 year on battery charger
3 years on motor
Limited lifetime on molded body parts


#### \*STANDARD CONFIGURATION

Chrome Telescoping Wand w/Button Lock  
10" Multi-Surface Floor Tool  
13" Crevice Tool  
5 ½" Upholstery Tool w/Removable Brush  
2 ½" Rectangular Dust Brush 90/180° Swivel

#### OPTIONAL CONFIGURATION

**107292** w/ GoCart Kit B (107290) **\$3,499**

# GOCARTVAC PARTS



No.	Product Name	Qty	List Price
1	104273 Twist Cap (Black)	1 ea.	\$ 28.85
2	100431 Intercept Micro Filter	10/pk	15.60
3	100564 Micro Cloth Filter	1 ea.	24.45
4	106282 Power Cord Replacement, Complete	1 ea.	65.87
5	105044 Motor Shroud/Diffuser w/Screw Set: 2 screws	1 set	22.48
6	100335 Compression Ring w/Connection Screws	1 set	11.15
	100378 Compression Ring Connection Screws	1 set	2.95
7	100014 Tetraseal	1 ea.	11.81
8	103732 36V Motor w/Crimps, Replacement	1 set	194.67
	103731 Carbon Brush Set for 36V motor	1 set	31.49
	103617 Complete 36V Motor Assembly w/Seal, Compression Ring and Control Module (includes: #6, 7, 8, 9)	1 set	312.90
9	105496 Battery Control Module	1 ea.	88.57
10	100368 Motor Mounting System Set	1 set	13.11
11	103916 Receptacle, 2-Wire w/Crimps	1 ea.	7.05
12	104272 Receptacle Screw Set	1 set	2.27
13	100030 Dome Filter w/Foam Media	1 ea.	7.88
	100343 Foam Filter Media for Dome Filter	1 ea.	1.32
	101220 High Filtration Disk (Optional) (2 pack)	2/pk	10.59
15	103623 Electrified Hose, 1 1/4" x 20' Long, 2-Wire	1 ea.	209.57
16	102715 Replacement Swivel Elbow Cuff, Black	1 ea.	9.66
17	106550 Switch Replacement	1 ea.	8.90
18	106284 Kit, Vacuum Attachment Hardware for Cart	1 ea.	2.85
19	106219 Kit, Power Receptacle Cord	1 set	15.05
20	106211 Box, Sound w/Corner Rails	1 set	484.31
21	106213 Cart Assembly Complete	1 ea.	462.00
22	106214 Kit, Mounting Hardware	1 set	17.31
23	103718 Hose Wrap, Blk	1 ea.	38.37
24	106241 Kit, Receptacle for Box Assembly	1 ea.	9.66
25	106215 Kit, Box Assembly	1 set	127.19
26	106277 Harness, Charging w/Connectors	1 ea.	85.17
27	106216 Kit, Battery Wiring Harness	1 set	108.14
28	106280 Lead, Wire, Battery, Fusible Link, Replacement #8AWG, w/Terminals	1 ea.	35.96
29	106279 Lead, Wire, Battery, Red, #8AWG, w/Terminals	1 ea.	28.13
30	106278 Harness, Battery	1 ea.	54.51
31	106217 Kit, Receptacle	1 set	60.19
32	106281 Switch Assembly w/Crimps	1 ea.	39.74
33	106218 Kit, Charger, 36V, 18.5A, w/Terminals	1 ea.	781.20
34	105828 Battery, Lead Acid, 12V, 37AH	1 ea.	272.54
35	106283 Kit, Attachment Hardware for Charger and Box Assembly	1 ea.	2.85
36	107294 Thermal Protector	1 ea.	14.39
37	106928 Exhaust Muffler	1 ea.	6.08
38	105790 2 Wire Electrified Hose Cord (15")	1 ea.	15.02
39	106297 Rear Wheel Set w/Axle	1 set	107.88
40	106298 Front Wheel	1 ea.	24.98
	101678 50' Extension Cord (Not Shown)	1 ea.	32.60
	834669 Hardware for Base Legs (Not Shown)	1 set	41.30