

# QuarterVac®

## PROTEAM BID SPECIFICATIONS BACKPACK VACUUM CLEANER

<b>BODY COMPOSITION</b>	Blow molded, high tensile strength, impact resistant, recyclable, memory retaining High-density Linear Polyethylene
<b>BODY DIMENSIONS</b>	6.5" cylinder, 24" in length top to bottom
<b>CAP</b>	Injection molded twist cap attaches to vac body by twisting onto body, does not require any latches, hinges, or additional hardware
<b>WEIGHT</b>	9.0 lbs
<b>BUMPER PROTECTION</b>	A soft 1 1/8" wide bumper, affixed to bottom of the vacuum for wall and furniture protection
<b>FILTRATION</b>	High Efficiency Four Level filtration (676 sq. in.) to include: 1. Reusable Intercept Micro Filter 2. Micro Cloth Filter with Integrated Rubber Vac Seal 3. Replaceable Dome filter (covering motor) 4. Sound reducing foam and foam air diffuser Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.
<b>SOUND LEVEL</b>	68 dBA
<b>MOTOR</b>	One-stage, single speed, thru-flow, mounted at the bottom of the vacuum body 6.2 Amps 65" Water lift 115 CFM Airflow 744 Watts/120 Volts 50-60 Hz Resetable Discrete Thermal Switch for Overtemp motor protection
<b>EXHAUST AIR</b>	Displaced by 2 1/2" thick Foam Diffuser filter with sound foam
<b>BACKPACK ASSEMBLY</b>	Ventilated two piece ergonomic unbreakable Santoprene™ frame with padded, adjustable shoulder and sternum strap system with accessory tool loops permanently attached to padded waist belt (54" length).
<b>POWER CORD</b>	Detachable 50 foot extension cord, 16/3 gauge with molded plug which attaches to the vacuum pig tail cord with exclusive molded on strain relief.
<b>POWER SWITCH</b>	Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.
<b>VACUUM HOSE</b>	Black, 56" long, 1 1/2" diameter, swivel cuff, and swivel elbow.
<b>CAPACITY</b>	Top loading, 6 quart filter capacity
<b>COMMON ATTACHMENTS</b>	1. Telescoping Wand or Two Piece Wand 2. 14" Xover® Floor Tool – for carpet or hard surface floors 3. 3" plastic vacuum dust brush 4. 5" plastic upholstery tool 5. 17" plastic crevice tool *Many other attachments available for specific needs.
<b>WARRANTY</b>	Parts, Labor and Motor - 3 year (except for wear and tear items) Molded housing – Lifetime warranty
<b>CERTIFICATION</b>	Certified in the United States and Canada to UL 1017/CSA C22.2 No. 243 by TÜV SÜD America. Certificate number: U8 10 12 62289 016.