

# GoFree Flex Pro 12Ah /6Ah

## PROTEAM BID SPECIFICATIONS BATTERY/BACKPACK VACUUM CLEANER

<b>BODY COMPOSITION</b>	Injection molded, impact modified polypropylene copolymer
<b>BODY DIMENSIONS</b>	7-1/8 x 10-1/8, 24" length top to bottom
<b>CAP</b>	Injection molded cap attaches to vac body by three die-cast aluminum latches
<b>WEIGHT</b>	19 lbs (12Ah) / 17 lbs (6Ah)
<b>BUMPER PROTECTION</b>	Dual shot injection molded bumper absorbs shocks when unit is dropped
<b>FILTRATION –</b>	Four Level HEPA 99.97% @ .3 Micron Filtration to include (1054 sq. in. total area): 1. Reusable Intercept Micro Filter 2. Micro Cloth Filter with Integrated Rubber Vac Seal 3. Replaceable Dome filter (covering motor) 4. 2 Replaceable HEPA Filters after the motor Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.
<b>SOUND LEVEL</b>	63.7 dBA LEED ISO 11201
<b>MOTOR</b>	one stage, single speed, flow-thru, mounted above the battery 12 Amps 65" Water lift 70 CFM Airflow 444 Watts/37 Volts DC Self-resetting thermal protector for Overtemp motor protection
<b>BATTERY</b>	12Ah - Approximately 60 minutes of continuous run time 6Ah – Approximately 30 minutes of continuous run time Battery Type – Lithium Polymer Lithium Ion Battery Module automatically shuts down the battery when it is ready to be charged.
<b>CHARGER</b>	12Ah - Approximately 2.5 hours to full charge time 6Ah – Approximately 1.5 hours to full charge time
<b>EXHAUST AIR</b>	Dispersed through 2 HEPA media filters
<b>BACKPACK ASSEMBLY</b>	Breathable mesh material with articulating harness, adjustable shoulder and sternum strap system with accessory tool loops permanently attached to padded waist belt (65" length).
<b>POWER SWITCH</b>	Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.
<b>VACUUM HOSE</b>	Black, 56" long, 1 1/2" diameter, swivel cuff, and swivel elbow.
<b>CAPACITY</b>	Top loading, 6 quart filter capacity
<b>COMMON ATTACHMENTS</b>	1. Telescoping Wand or Two Piece Wand 2. 14" Xover® Floor Tool – for carpet or hard surface floors 3. 3" plastic vacuum dust brush 4. 5" plastic upholstery tool 5. 17" plastic crevice tool *Many other attachments available for specific needs.
<b>WARRANTY</b>	2 years – motor, battery, charger, 3 years on parts and labor. (except for wear and tear items) Molded housing – Lifetime warranty Articulating harness – 3 years (except for wear and tear items)
<b>CERTIFICATION</b>	This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)

