

**Super Coach Pro™ 6**  
**PROTEAM BID SPECIFICATIONS**  
**BACKPACK VACUUM CLEANER**

<b>BODY COMPOSITION</b>	Injection molded, impact modified polypropylene copolymer
<b>BODY DIMENSIONS</b>	7-1/8 x 10-1/8, 18.5" length top to bottom
<b>CAP</b>	Injection molded cap attaches to vac body by three die-cast aluminum latches
<b>WEIGHT</b>	Body: 9.6 lbs, Harness: 2 lbs
<b>BUMPER PROTECTION</b>	Dual shot injection molded bumper absorbs shocks when unit is dropped
<b>FILTRATION</b>	Four Level HEPA 99.97% @ .3 Micron Filtration to include (1054 sq. in. total area): 1. Reusable Intercept Micro Filter 2. Micro Cloth Filter with Integrated Rubber Vac Seal 3. Replaceable Dome filter (covering motor) 4. 2 Replaceable HEPA Filters after the motor Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.
<b>SOUND LEVEL</b>	65.8 dBA
<b>MOTOR</b>	One-stage, single speed, thru-flow, mounted at the bottom of the vacuum body 9.5 Amps 96" Water lift 159 CFM Airflow 1108 Watts/120 Volts 50-60 Hz Resetable Discrete Thermal Switch for Overtemp motor protection
<b>EXHAUST AIR</b>	Displaced by 2 HEPA media filters
<b>BACKPACK ASSEMBLY</b>	Breathable mesh material with articulating harness, adjustable shoulder and sternum strap system with accessory tool loops permanently attached to padded waist belt (65" length).
<b>POWER CORD</b>	Detachable 50 foot extension cord, 16/3 gauge with molded plug which attaches to the vacuum pig tail cord with exclusive molded on strain relief.
<b>POWER SWITCH</b>	Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.
<b>VACUUM HOSE</b>	Black, 56" long, 1 1/2" diameter, swivel cuff, and swivel elbow.
<b>CAPACITY</b>	Top loading, 6 quart filter capacity
<b>COMMON ATTACHMENTS</b>	1. Telescoping Wand or Two Piece Wand 2. 14" Xover® Floor Tool – for carpet or hard surface floors 3. 3" plastic vacuum dust brush 4. 5" plastic upholstery tool 5. 17" plastic crevice tool *Many other attachments available for specific needs.
<b>WARRANTY</b>	Parts, Labor and Motor - 3 year (except for wear and tear items) Molded housing – Lifetime warranty Articulating harness – 3 years (except for wear and tear items)
<b>CERTIFICATION</b>	This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243)