



# GoFree<sup>®</sup> Flex Pro

WORK WITHOUT RESTRICTIONS

Approx. 75 minutes of runtime - Our longest runtime yet brings unparalleled productivity.

# THE FUTURE OF EFFICIENCY IS HERE

Unequaled Comfort in a Battery Powered Backpack Vacuum



**BETTER BALANCE**  
move more confidently and comfortably with our lightest cordless unit

**LIGHTWEIGHT**  
at only 18 pounds, the GoFree Flex Pro is one of the lightest battery backpacks on the market

**LONGER-LASTING BATTERY PERFORMANCE**  
Lithium Ion battery and control circuit for state-of-the-art performance

**NOTICEABLY QUIETER**  
only 63.7 dBA

**EASY-TO-READ CHARGE STATUS**  
a lighted display allows you to see charge levels on-the-go

**FREEDOM OF MOVEMENT**  
articulating FlexFit harness is responsive to the motion of the user's shoulders, back and hips—increasing comfort and reducing fatigue

**REDUCED EMISSIONS**  
easy access post-motor HEPA media filters capture and contain microscopic particulate and carbon motor dust

**CORDLESS CONVENIENCE**  
set yourself free from the restriction of a cord and eliminate cord management tasks

**FAST CHARGE**  
battery reaches optimum charge in just 2.5-3 hours so you can get up and GoFree again and again

**LONGER RUNTIME**  
no other battery backpack compares to the GoFree's approximate 75-minute runtime

## THE MOVEMENT IS HERE

You've never cleaned like this before.

The enhanced GoFree® Flex Pro with new state-of-the-art Lithium Ion battery and approximate **75-minute runtime**. The GoFree Flex Pro cordless backpack vacuum now cleans **30% faster** than a corded backpack and **5x faster** than an upright vacuum. Durable, reliable, and more comfortable than ever, the GoFree Flex Pro provides ultimate cleaning freedom.



# JOIN THE MOVEMENT

## New and Improved

The enhanced GoFree Flex Pro is one of the lightest battery backpacks on the market and includes an upgraded FlexFit® Articulating Harness. Thicker back and shoulder pads create more comfortable contact points, so cleaners can vacuum longer with greater comfort. Easy adjustments allow for an ergonomic fit on a wide range of body types.

Suited to challenging environments, the GoFree Flex Pro cleans stairwells, high places, and around obstacles without tethering the cleaner to the nearest outlet. In high-traffic areas or 24-hour facilities, the GoFree Flex Pro can move among building occupants without presenting a tripping hazard. Running at only 63.7 decibels, it cleans without disturbing conversations nearby.

## FREEDOM OF MOVEMENT



	GoFree Flex Pro
Airflow	78 CFM
Static Lift	54 in
Power	360 W, 36 Volts DC
Decibel	63.7 dBA
Capacity	6 qt. / 6.6 L
ProLevel Filtration™	1054 sq. in total area
Warranty	3 years - parts, labor 2 years - motor, battery & charger Lifetime - molded body parts
Battery Type	Lithium Ion
Charge Cycles	up to 850
Certification	UL Listed to US and Canadian safety standards.
Weight	18 lbs.
Approx. Runtime	75 min.
Approx. Charge Time	2.5 - 3 hrs to full charge

PERFORMANCE SPECS BASED ON MOTOR SPECS



[proteam.emerson.com](http://proteam.emerson.com)



866.888.2168 | [customerservice.proteam@emerson.com](mailto:customerservice.proteam@emerson.com)

ProTeam, GoFree, FlexFit and ProLevel Filtration are trademarks and registered trademarks of ProTeam, Inc. © 2017 ProTeam, Inc. All Rights Reserved. As a Proud Partner, ProTeam supports the American Lung Association's clean indoor air initiatives. The American Lung Association does not endorse products.