

SUPER COACHVAC[®]

PROTEAM BID SPECIFICATIONS BACKPACK VACUUM CLEANER

BODY COMPOSITION	Blow molded, high tensile strength, impact resistant, recyclable, memory retaining High-density Linear Polyethylene
BODY DIMENSIONS	8.5" cylinder, 25" in length top to bottom
CAP	Injection molded twist cap attaches to vac body by twisting onto body, does not require any latches, hinges, or additional hardware
WEIGHT	11 lbs
BUMPER PROTECTION	A soft 1 1/8 inch wide bumper, affixed to bottom of the vacuum for wall and furniture protection
FILTRATION	High Efficiency 4-level Filtration (1136 sq.in.)to include: 1. Reusable Intercept Micro Filter @ 698 inches of filtration media 2. SEMS Cloth filter with Integrated Rubber Vac Seal 3. Dome filter with replaceable media filter (covering motor) 4. Sound reducing foam and foam air diffuser
SOUND LEVEL	66 db
MOTOR	One stage, single speed, thru-flow, mounted at the bottom of the vacuum body 9.9 Amps 100" Water lift 150 CFM Airflow 1188 Watts/120 Volts 50-60 Hz Resetable Discrete Thermal Switch for Overtemp motor protection
EXHAUST AIR	Displaced by 2 1/2" thick washable Foam Diffuser filter with sound foam
BACKPACK ASSEMBLY	Ventilated ergonomic unbreakable Santoprene™ frame with padded, adjustable shoulder and sternum strap system and accessory tool loops permanently attached to padded waist belt.
POWER CORD	Detachable 50 foot extension cord, 16/3 gauge with molded plug which attaches to the 14/3 gauge vacuum pig tail cord with exclusive molded on strain relief. Schulte Cord Management System
POWER SWITCH	Heavy duty double pole rocker type switch mounted in a switch box and conveniently attached with Velcro™ to the left side of waist belt. Switch cord is 14/4 gauge with exclusive molded on strain relief.
VACUUM HOSE	56" long, 1 1/2" diameter, static dissipating
CAPACITY	Top loading, 10 quart filter capacity

SUPER COACH VAC®

PROTEAM BID SPECIFICATIONS BACKPACK VACUUM CLEANER

Page II

COMMON ATTACHMENTS	<ol style="list-style-type: none">1. 2 piece 56" aluminum two-bend wand, w/button lock, 1 ½" in diameter2. 14" E-Z Glide® floor tool(w/ replacable brush) – for carpet or hard surface floors3. 3" plastic vacuum dust brush4. 5" plastic upholstery tool5. 17" plastic crevice tool6. 14" Floor Tool, W/Scallops for carpet <p>*Many other attachments available for specific needs.</p>
WARRANTY	<p>3 year on Parts, Labor and Motor - (except for wear and tear items) Lifetime warranty, Molded body <u>Santoprene™ backplate – Lifetime warranty (excludes harness assembly)</u></p>
CERTIFICATION	<p>Fully certified by <u>CSA/NRTL</u>. This means that they are certified in the United States (equivalent to UL certification)as well as in Canada. File #LR-80972</p>

PROTEAM UNIQUE FEATURES

EDUCATIONAL MATERIALS	<p>Backpack Vacuum training video, The ProTeam Way & Set-Up/ Training/Operation DVD School training video – Vacuuming in the Educational Environment Team Cleaning Videos: Team Cleaning Over View Vacuum Specialist Restroom Specialist Light Duty Specialist</p>
-----------------------	--

May 21 2010