


ProTeam LineVacer® HEPA / ULPA

100277* LineVacer HEPA w/ High Filtration Vacuum Tool Kit (100163) **\$1,070**

The ProTeam LineVacer HEPA / ULPA backpack vacuum is equipped with a unique Four Level® Filtration system which utilizes a certified HEPA or ULPA filter as the last filtration stage. The certified HEPA filter is 99.97% efficient at filtering particulates down to 0.3 microns in size and is designed so that all particulate drawn into the vacuum is expelled through the HEPA filter with no air leaking past it. The LineVacer is ideal for applications when clean air in a controlled environment is critical such as cleaning medical facilities, clean rooms and computer labs. This vacuum meets the EPA's definition of a HEPA Vacuum under the Lead Safety Renovation, Repair and Painting Rule (EPA RRP Rule).



HEPA/ULPA



INDOOR
AIR
QUALITY



PERFORMANCE

Specifications

Weight:	13 lbs. / 5.9 kg.
Motor Airflow:	124 CFM
Static Lift:	75 in.
Motor:	744 W / 6.2 A
Decibel:	64 dBA
Capacity:	10 qt. / 11 L
Four Level® Filtration w/HEPA:	2283 sq. in. total area
Four Level Filtration w/ULPA:	3232 sq. in. total area

HEPA / ULPA Filtration

- HEPA: 99.97% at 0.3 microns
- ULPA: 99.999+% at 0.12 microns

Limited Warranty

- 3 years parts, labor and motor on vacuum
- Limited lifetime on molded body parts

*Standard Configuration

Two-Piece Aluminum Wand w/Button Lock	5" Upholstery Tool
36" One-Bend Bulk Pick-Up Tool	3" Dust Brush
14" Carpet Tool w/Scallops	

Related Products


100291	Intercept Micro® Filters, 10/pk (closed collar)	\$40.83
--------	---	---------

Optional Configurations

100280	ULPA w/High Filtration Vacuum Tool Kit (100163)	\$1,290
107141	HEPA w/Xover® Performance Telescoping Wand Tool Kit C (107099)	1,070
107161	HEPA w/Turbo Brush Tool Kit (107162)	1,150
107471	HEPA w/Remediation Tool Kit (107466)	1,140

Specification calculations are based on average motor performance.

LINEVACER PARTS



No.	Product Name	Qty	List Price
1	104276 Latch Cap w/Cuff (Black)	1 ea.	\$ 95.96
2	100291 Intercept Micro Filter	10/pk	40.83
3	100565 Micro Cloth Filter	1 ea.	43.72
4	100286 Top or Bottom Cap Latch Set: 3 Latches, 3 Locks w/6 Fastening Rivets, 6 Washers	1 set	57.23
5	510738 Cord Holder	1 ea.	3.95
6	100356 Shoulder Strap Assembly (includes: 7a, 7b)	1 set	25.19
	100354 Strap Assembly Complete (includes: 6, 12)	1 set	77.48
7a	100358 Shoulder Strap Plastic Adjustment (Top)	1 ea.	1.49
7b	100357 Shoulder Strap Plastic Adjustment (Bottom)	1 ea.	1.49
8	105046 Backplate (includes: 9)	1 ea.	38.74
9	100375 Barrel Nut Connection Set for Backplate (Replacement)	1 set	8.75
10	100374 Backplate Connection Set: 4 Screws w/Washers, Stand Offs	1 set	19.37
11	106719 Waist Belt Keeper and Latch	1 ea.	17.57
12	100359 Waist Belt (includes: 11)	1 ea.	58.09
13	103166 Backplate System Complete (includes: 5-12)	1 set	96.84
14	100641 Power Cord Assembly Complete	1 set	28.11
15	101610 Switch Cord Assembly 120V (includes: 16, 17)	1 set	54.26
	101714 Switch Cord w/Crimps	1 ea.	24.06
16	101472 Switch Box w/Velcro and New Lamb Switch	1 set	34.86
	106287 Switch Box w/Velcro and Screws	1 ea.	26.03
17	106066 On/Off Switch (must use with #106287)	1 ea.	10.56
18	104275 ULPA Filter Assembly Complete w/Bottom Cap	1 set	494.51
	(100280, 100282)		
19	104274PT HEPA Filter Assembly Complete w/Bottom Cap	1 set	358.19
	(100277, 100279)		
20	100335 Motor Compression Ring w/Screws	1 set	18.63
	100378 Compression Ring Screw Set: 4 Screws	1 set	4.38
21	100014 Motor Gasket	1 ea.	17.47
	100297 Gasket Ring (Not Shown)	1 ea.	7.63
22	105697 Carbon Brush Set (Domel Motor)	1 set	30.98
	100424 Carbon Brush Set (Ametek Motor) (116311-00)	1 set	30.98
	106904 Carbon Brush Set (Ametek Motor) (122157-00)	1 set	30.98
23	100422 Motor/Fan (120 V) w/Crimps (Ametek Motor)	1 ea.	134.27
	100380 Motor Crimp Set: 4 female, 4 Male and a Ground Crimp Connector	1 set	15.52
	100379 Motor Ground, Wire Clamp Set w/Screws	1 set	8.75
24	100368 Motor Mounting System Set: 3 Well Nuts, 3 Bolts, 3 Washers, 3 Covers	1 set	19.37
25	100030 Dome Filter w/Foam Media	1 ea.	11.66
26	100343 Foam Filter Media for Dome Filter	1 ea.	2.69
27	107648 48" Static-Dissipating Hose w/ Non-Replaceable Elbow and Straight Cuffs	1 ea.	40.47
28	101928 Replacement Double Swivel Elbow Cuff	1 ea.	13.40
29	100694 Replacement Double Swivel Straight Cuff	1 ea.	7.99
30	107294 Thermal Protector	1 ea.	21.27
31	105044 Motor Shroud/Diffuser w/Screw Set: 2 Screws	1 set	33.21
	101678 50" Extension Cord (Not Shown)	1 ea.	49.64