

ProTeam ProBlitz®

107132 ProBlitz
107596 ProBlitz XP

\$375
\$450

ProBlitz XP now features daisy chain receptacles where user can connect 2 additional air movers for large area drying. Maximum airflow and low amp draw combine to make the ProBlitz AirMover the first choice for Carpet Cleaners and Restoration Contractors alike. With 3 fan speeds and 3 operating positions, the ProBlitz AirMover tackles every air circulation requirement with ease.



*ProBlitz XP AirMover shown.

Specifications

Motor:	.4 HP / 360 Watt / Capacitor	
Amperage:	Low	2.4 A
	Medium	2.7 A
	High	3.0 A
Motor Airflow:	2200 CFM (max)	
Weight:	28 lbs. / 12.7 kg.	
Decibel:	Low	63 dBA
	Medium	65 dBA
	High	66 dBA
Housing:	2-Piece High-Impact Polypropylene w/Built-in Cord Wrap	
Storage:	Vertically stackable and top-mounted carry handle	
Blower Wheel:	High-Impact Polypropylene	
Drying Positions:	Three - 0°, 45° / 60° (XP model only), 90°	
Transportation:	Telescoping handle and wheels (XP model only)	
Power Cord:	ProBlitz - 30'	
	ProBlitz XP - 25'	
Circuit Breaker:	8 amp max (XP model only)	

Related Products


107300 Carpet Clamp Kit \$77.16

Specification calculations are based on average motor performance.

Limited Warranty

- 3 years parts, labor and motor on vacuum
- Limited lifetime on molded housing

PROBLITZ AIRMOVER PARTS



No.	Product Name	Qty	List Price
1	510141 Switch & Knob Assembly	1 ea.	\$ 13.09
2	833658 Inlet Grill	1 ea.	9.78
	510551 Inlet Grill with Outlets (ProBlitz XP)	1 ea.	19.54
3	820563-7 Screw, Type AB #10 x 3/4"	1 ea.	0.71
4	833673 Threaded Inserts - Housing	1 ea.	10.44
5	820563-7 Screw, Type AB #10 x 3/4"	1 ea.	0.71
6	820563-13 Screw, Type AB #10 x 1"	1 ea.	0.71
7	510140 Wheel Assembly (ProBlitz XP)	1 ea.	15.97
8	820563-7 Screw, Type AB #10 x 3/4" (ProBlitz XP)	1 ea.	0.71
9	833690 Foot Bumper	1 ea.	11.76
	(Only four (4) required for ProBlitz XP)		
10	820563-7 Screw, Type AB #10 x 3/4"	1 ea.	0.71
	(Only four (4) required for ProBlitz XP)		
11	833659 Exhaust Grill	1 ea.	8.23
12	833674 Motor	1 ea.	165.94
13	833675 30' Cord w/Plug	1 ea.	38.85
	841368 25' Cord w/Plug (ProBlitz XP)	1 ea.	60.54
14	833660 Blower Wheel	1 ea.	45.18
15	833691 Retractable Handle (ProBlitz XP)	1 ea.	43.78
16	820563-7 Screw, Type AB #10 x 3/4" (ProBlitz XP)	1 ea.	0.71
17	833657-1 Housing (left side)	1 ea.	32.58
18	833656-1 Housing (right side)	1 ea.	46.35