



Our Cordless GoFree[®] Flex Pro II

Experience **longer run times**, **lighter weight**
and a **high/low power switch** for
greater **efficiency**.

 ProTeam[®]



Boost Productivity

You've never cleaned like this before.

With a high/low power switch, the GoFree Flex Pro II brings greater versatility and comfort to professional cleaners. By cleaning at a rate 30% faster than a corded backpack and 5x faster than an upright vacuum, the GoFree Flex Pro II will save you time and money. Created by the company of productivity, durability and clean-air vacuums.



**CORDLESS
EFFICIENCY**



**HIGH/LOW
POWER SWITCH**

High - High Traffic,
Deep Clean
Low - Daily Clean



LIGHTWEIGHT

17.5 lbs.





GOFREE FLEX PRO II
ProLevel Filtration® w/ HEPA media captures 99.972%; avg. @ .3-5µm
ProLevel Filtration® avec matériau HEPA, capture 99,972 % en moyenne @ 0,3-5,0 µm

FREEDOM OF MOVEMENT

FlexFit® articulating harness is responsive to the motion of your shoulders, back and hips — increasing comfort and reducing fatigue

NOTICEABLY QUIETER BRUSHLESS MOTOR

Only 63.9 dBA (low) and 65.9 dBA (high) and with no carbon brushes to change, the motor has a longer life and emits no carbon dust

HIGH/LOW SETTINGS

Conserve runtime by tackling routine cleaning on low, then switch to high for deep cleaning

EASY TO READ CHARGE STATUS

Lit display allows you to see charge levels

CLEAN AIR BACKPACK

ProLevel Filtration® system, featuring multiple levels of filters, helps reduce allergens and asthma triggers in the indoor environment





Cordless cleaning

Lightweight cordless vacuums set you free from restrictions. Without the potential tripping hazard of a cord, vacuuming is safer and easier. Cordless vacuums eliminate time-consuming cord management tasks and allow you to take the most efficient path through a space.

Clean more than just hard surfaces.



| | GoFree Flex Pro II |
|--|--|
| Weight | 17.5 lbs. / 7.9 kg. |
| Motor Airflow | 58 CFM (low) 65 CFM (high) |
| Static Lift | 67 in. (low) 81 in. (high) |
| Power | 36 VDC / 240 W (low) 345 W (high) |
| Decibel | 63.9 dBA (low) 65.9 dBA (high) |
| Capacity | 6 qt. / 6.6 L |
| Battery Type | Lithium Ion, 12Ah |
| Approx. Runtime | 106 min. (low) 75 min. (high) |
| Approx. Full Charge Time | 3 hrs. |
| Minimum Charge Cycles | 1000 |
| ProLevel Filtration* w/ Four Levels of Filtration | 1054 sq. in total area |
| *ProLevel Filtration System with HEPA Media | Captures 99.72% at 0.3-.5 microns per ASTM F3150 |
| Warranty | 3 yrs - parts, labor 2 yrs - motor, battery & charger Limited Lifetime - molded body parts |
| Certification | UL Listed to US and Canadian safety standards. |

CFM = Cubic Feet per Minute dBA = A-Weighted Decibel Value Ah = Amp Hours

SPECIFICATION CALCULATIONS ARE BASED ON AVERAGE MOTOR PERFORMANCE.

*The filtration value of ProTeam's ProLevel Filtration System in this vacuum is achieved by the use of a multi-stage filtration system, including intercept micro filter, micro cloth filter, plastic cage with foam filter, and post-motor filter made from HEPA media, as tested per ASTM F3150.



proteam.emerson.com • 866.888.2168 • customerservice.proteam@emerson.com

