

ProGuard® 10
PROTEAM BID SPECIFICATIONS
WET/DRY VACUUM CLEANER

| | |
|---------------------------|---|
| BODY COMPOSITION | Polypropylene Motor cover, collector and HDPE tank. |
| BODY DIMENSIONS | 21L" X, 16.8"W X 24.9"H |
| CASTERS | 4 - 3" Soft Ride Swivel |
| WEIGHT | 28 lbs (12.7 kg) |
| FILTRATION | Intercept Micro Filter, Optional Patent Pending 3 Layer Fine Dust Cartridge, 1276 sq. in. Patent Pending Wet Filter, 105 sq. in. (Polypropylene screen) |
| SOUND LEVEL | 68 dBA |
| MOTOR | Two-Stage By-Pass Motor 95" Water lift 105 CFM Airflow 1380 Watts 9.5 Amps 15A, 120 VAC, 121C rating (Thermodisc) Overtemp motor protection |
| POWER CORD | 50" 14 AWG with Twist-Lock Pigtail Connection |
| POWER SWITCH | Single pole, single throw, 15A/125VAC rating |
| VACUUM HOSE | 10' Hose, 1 1/2" diameter, secure lock |
| CAPACITY | 10 Gallon (38 liter), Includes float system over motor to prevent tank overflow, and motor from debris and moisture damage. |
| COMMON ATTACHMENTS | 1. Two piece wand, button-lock, 1 1/2" in diameter 2. Bristle Floor Tool 3. Squeegee Tool 4. Crevice Tool 5. Dust Brush |
| WARRANTY | 3 year on Parts, Labor and Motor - (except for wear and tear items) Lifetime warranty, Molded body Parts * See owner's manual for complete warranty details |
| CERTIFICATION | This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards (UL1017 & CSA C22.2 No 243) |

3/17/16