



Innovative Features, Powerful Suction and Advanced Maneuverability

Upright Vacuums

 **ProTeam**[®]

UPGRADE YOUR UPRIGHT



FIRST LINE OF DEFENSE

The Intercept Micro® Filter is the first of a multi-stage filtration system that helps improve Indoor Air Quality.

ProTeam ProGen® 12 & 15

Clean Better with Advanced Features

The ProGen has the added performance and features to make it an instant hit with cleaning professionals. Choose 12" or 15" width for productivity in a variety of applications.

EXCLUSIVE ANIMATED DASHBOARD

Alerts user to brush roll jam, airflow block or full filter

LED LIGHTS THE WAY

Ultra-bright LED headlamps illuminate the cleaning path

ADVANCED MANEUVERABILITY

Large rubberized wheels allow smooth movement, tight turning radius and easy threshold clearance

EFFICIENT DETAILING

Premium on-board tools allow detail cleaning with maximum efficiency

HEALTHIER AIR

Dual post-motor HEPA media filters capture and contain allergens and asthma triggers

MULTIPLE CLOG PORTS

Remove clogs without tools through four access points: under the powerhead, at both ends of the hose, and where the wand attaches to the base

EXTENDED REACH

Clean hard-to-reach areas with 24-inch wand & hose that stretches to 8 feet

COST OF OWNERSHIP

Durable construction, easy maintenance & 3-year limited warranty assure a higher return on investment

SERVICE WITHOUT TOOLS

Clear blockages & remove brush roll without using tools



DUAL MOTOR PERFORMANCE

Turn off the brush roll to vacuum hard surfaces without scratching them and turn it on for carpets

ProTeam ProForce® 1200XP & 1500XP

Exceptional Cleaning & High-Filtration

The ProForce uprights provide exceptional cleaning in a high-filtration upright. Choose 12" or 15" width for productivity in a variety of applications.

WITHSTANDS HEAVY-DUTY USE

High-impact molded plastic to withstand tough cleaning conditions

POWERFUL SUCTION

The high-performance dual motor system maintains power to both the brush roller and the suction motor

LIGHTED DISPLAY

Alerts user to full filter, brush roller on or jammed brush roll

COST OF OWNERSHIP

High-impact durable construction and a 3-year warranty limited warranty make for less spent on owning the ProForce

INNOVATIVE DESIGN

Low profile, L-shaped head perfect for vacuuming under and around furniture and across different types of flooring

WEIGHT DISTRIBUTION

Light weight construction allows for easier operation and less operator fatigue



PREMIUM ON-BOARD TOOLS

Easily accessible on-board tools with a convenient wand for detail cleaning and hard-to-reach areas.

"Great for an office environment."

Jonathan Lewis | Memphis, Tennessee

"Lightweight, suction is better & it cut down time."

Walter Mitchell | Wilwood, Missouri

"I thought this vacuum was easy to maintain & use."

Doug Hewling | Cincinnati, Ohio

"Love the clean-out mechanism."

Kevin Fox | Meadville, Pennsylvania

SINGLE OR DUAL MOTOR OPTIONS

Professional and Innovative Commercial Cleaning

Our top-of-the-line uprights have evolved into superior cleaning machines. These vacuums provide exceptional cleaning in high filtration uprights to improve reach, durability, and Indoor Air Quality. Multiple head widths allow cleaners to choose the best path for their facilities.

	107329 ProGen 12 107330 ProGen 15	107251 ProForce 1200XP 107252 ProForce 1500XP
Weight	17 lbs. / 7.71 kg. (12"), 18 lbs. / 8.17 kg. (15")	18 lbs. / 8.17 kg.
Handle Weight	2.7 lbs. / 1.22 kg.	4.7 lbs. / 2.13 kg.
Airflow	100 CFM	96 CFM
Static Lift	93 in	84 in
Power	1100 W	924 W Dual Motor
Amperage	9.8 A	10 A
Decibel	69 dBA	67 dBA
Capacity	3.25 qt. / 3 L	3.25 qt. / 3 L
ProLevel Filtration® w/HEPA Media	captures up to 97.44% at .3 microns (12") captures up to 98.36% at .3 microns (15")	captures up to 97.33% at .3 microns (12") captures up to 98.73% at .3 microns (15")
Cord Length	40' (12"), 50' (15")	50'
Warranty	3 years - parts, labor, motor and molded body parts (except wear items)	3 years - parts, labor, motor and molded body parts (except wear items). 2 years - ProForce brush roll motor (104506)
Certification	UL Listed to US and Canadian Safety Standards (UL 1017/CSA C22.2 No 243), CRI Seal of Approval, CRI Rating - Certified Silver	UL Listed to US and Canadian Safety Standards (UL 1017/CSA C22.2 No 243), CRI Seal of Approval, CRI Rating - Certified Bronze

To Reorder Intercept Micro Filters:

Contact your local ProTeam distributor or ProTeam Customer Service to find a local distributor. Filters can also be purchased at proteam.emerson.com.

107377 Intercept Micro Filter for ProGen



103483 Intercept Micro Filter for ProForce



proteam.emerson.com



866.888.2168 | customerservice.proteam@emerson.com

ProTeam, ProForce, ProGen, Intercept Micro and ProLevel Filtration are trademarks and registered trademarks of ProTeam, Inc. © 2014-2024 ProTeam, Inc. All Rights Reserved.

The American Lung Association and ProTeam are partners in an educational campaign about Indoor Air Quality issues. The American Lung Association does not endorse product, device or service.