



ProTeam ProGuard® 15

PROTEAM BID SPECIFICATIONS

WET/DRY VACUUM CLEANER

Physical Components

- Body Composition - Polypropylene motor cover, collector and HDPE tank.
- Capacity - 15 gallon (57 liter), includes float mechanism to prevent tank overflow & protect motor from debris & moisture damage, dual drain feature tip & pour or drain hose.
- Power Cord - 50" 14 AWG with twist-lock pigtail connection.
- Power Switch - Single pole, single throw, 15A/125VAC rating.
- Motor - Two-stage by-pass motor, 15A, 120 VAC, 121C rating (thermodisc) overtemp motor protection.
- Cart System - Ergonomic handle system, rear or center wheel position options.
- Casters/Wheels - Unique variable wheel pattern for increased maneuverability, 2-10" wheels, 2 - 4" casters.

Specifications

Body Dimensions:	21.5" L x 30" W x 41.25" H
Weight:	68 lbs./31 kg
Motor Airflow:	105 CFM
Static Lift:	95"
Motor:	1380 W/9.5 A
Decibel:	69 dBA
Tank Size:	15 gallon/57 L
ProGuard Wet Filter:	Polypropylene screen
Fine Dust Cartridge Filter:	1142 sq. in.
Vacuum Hose:	10' L, 1 1/2" diameter, static-dissipating, secure lock
Power Cord:	50', 14 AWG

Limited Warranty

- 3 years on parts, labor, and motor on vacuum
- Limited lifetime on molded body parts

Standard Attachments

Two-Piece Wand	Crevice Tool
14" Squeegee Tool	3" Dusting Brush
14" Hard Floor Tool w/Nylon Brush	

* Optional Front Mount Squeegee



Filtration

- Intercept Micro® Filter, Optional
- 3 Layer Fine Dust Cartridge, 1142 sq. in.
- Wet Filter, 105 sq. in. (Polypropylene screen)

Certification

This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards.