



ProBlitz XP Shown

## ProTeam ProBlitz® AirMover

### PROTEAM BID SPECIFICATIONS WET/DRY VACUUM CLEANER

#### Specifications

|                   |                                                        |
|-------------------|--------------------------------------------------------|
| Body Dimensions:  | 16.5" L x 20" W x 19.5" H                              |
| Motor:            | .4 HP/360 Watt/Capacitor                               |
| Amperage:         | Low 2.4 A<br>Medium 2.7 A<br>High 3.0 A                |
| Motor Airflow:    | 2200 CFM (max)                                         |
| Weight:           | 28 lbs./12.7 kg                                        |
| Decibel:          | Low 63 dBA<br>Medium 65 dBA<br>High 66 dBA             |
| Housing:          | 2-Piece high-impact polypropylene w/built-in cord wrap |
| Storage:          | Vertically stackable and top-mounted carry handle      |
| Blower Wheel:     | High-Impact polypropylene                              |
| Drying Positions: | Three - 0°, 45°/60° (XP model only), 90°               |
| Transportation:   | Telescoping handle and wheels (XP model only)          |
| Power Cord:       | ProBlitz - 30'<br>ProBlitz XP - 25'                    |
| Circuit Breaker:  | 8 amp max (XP model only)                              |

#### Limited Warranty

3 years on parts, labor, & motor on vacuum  
Limited lifetime on molded body parts

#### Features

Daisy Chain Receptacles - Connect 2 additional air movers for large area drying; Perfect for this low amp draw blower.

Prevention - Prevent permanent damage to flooring with 3 fan speeds.

Easy Transport - XP model with telescoping handle and wheels.

Flexibility - Three operating positions to direct air where you need it.

Stackable - Convenient storage and transport.

#### Certification

This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards.