



ProTeam ProVac® FS6

PROTEAM BID SPECIFICATIONS BACKPACK VACUUM CLEANER

Physical Components

Body Composition - Rotational molded, high tensile strength, impact resistant, recyclable, memory retaining high-density linear polyethylene.

Cap - Injection molded twist cap attaches to vac body by twisting onto body, does not require any latches, hinges, or additional hardware.

Power Cord - Detachable 50 foot extension cord, 16/3 gauge with molded plug.

Power Switch - Heavy duty double pole single throw, rocker type switch integrated into the waist belt assembly for easy ergonomic access.

Backpack Assembly - Ventilated two piece ergonomic unbreakable Santoprene™ frame with padded, adjustable shoulder and sternum strap system with accessory tool loops permanently attached to padded waist belt (54" L).

Exhaust Air - Displaced by 2 1/2" thick Foam Diffuser filter with sound foam.

Motor - Two-stage, single speed, thru-flow, mounted at the bottom of the vacuum body, 50-60 Hz resetable discrete thermal switch for overtemp motor protection.

Specifications

Body Dimensions:	10.125" L x 7.125" W x 18" H
Weight:	11.6 lbs./5.25 kg
Motor Airflow:	153 CFM
Static Lift:	91 in.
Motor:	1108 W/9.5 A
Decibel:	69.7 dBA
Capacity:	6 qt./6.6 L
ProLevel Filtration* w/Four Levels of Filtration:	1054 sq. in. total area
Vacuum Hose:	48" long, 1 1/2" diameter
Exhaust Air:	2 1/2" foam diffuser filter
Bumper Protection:	1 1/8 inch soft bumper

Limited Warranty

3 years parts, labor and motor on vacuum

Limited lifetime on molded body parts

Standard Attachments

14" Hard Floor Tool w/Nylon Brush	5" Upholstery Tool
Two-Piece Aluminum Wand w/Button Lock	3" Dust Brush
14" Carpet Tool w/Scallops	11" Crevice Tool



*ProLevel Filtration® System w/HEPA Media

captures 99.63% at 0.3-.5 microns per ASTM F3150

ProLevel Filtration System includes:

1. Reusable Intercept Micro® Filter
2. Micro Cloth Filter with Integrated Rubber Vac Seal
3. Replaceable Dome Filter (covering motor)
4. (2) Replaceable Exhaust Filters Made from HEPA Media

*The filtration value of ProTeam's ProLevel Filtration System in this vacuum is achieved by the use of a multi-stage filtration system, including intercept micro filter, micro cloth filter, plastic cage with foam filter, and post-motor filter made from HEPA media, as tested per ASTM F3150.

Certification

This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards.