



ProTeam ProGen® 12

PROTEAM BID SPECIFICATIONS

UPRIGHT VACUUM CLEANER

Physical Components

Body Composition - Injection molded, high tensile strength, impact resistant, recyclable, memory retaining ABS.

Cap - Injection molded cap secured cam lock closure.

Power Cord - Quick change replaceable power cord, 18/3 gauge with molded plug which attaches with an exclusive molded plug, quick release cord wrap.

Power Switch - Heavy duty rocker type switch mounted in the handle.

Motor - Single motor, 50-60 Hz, automatic thermal shut off switch – safety device, clutch protected drive system / auto shutoff if brush jams, anti-slip cogged belt drive for powerhead motor, long life 8mm belt width.

Maintenance - Remove clogs through 4 access points: under powerhead, at both ends of the hose, where the wand attaches to the base. Brush roll removed without tools.

Animated Light Display - Alert user of full bag, brush jam and clog issues. LED front lights brighten the cleaning path.

Specifications

Body Dimensions	12" L x 13" W x 47" H
Weight:	17 lbs./7.71 kg
Handle Weight:	2.7 lbs./1.22 kg
Motor Airflow:	100 CFM
Static Lift:	93 in.
Motor:	1100 W/9.8 A
Decibel:	69 dBA
Capacity:	3.25 qt/3 L
ProLevel Filtration® w/Three Levels of Filtration:	236 sq. in. total area
Cord length:	40'
Wheels:	Large rubber 3" wheels
Vacuum Hose:	1 1/2" diameter, 8 ft. long
Exhaust Air:	Displaced by 2 HEPA media filters
Bumper Protection:	Soft 1" wide bumper

Limited Warranty

3 years parts, labor, motor and molded body parts (except for wear items)

Standard Attachments

Upholstery Tool
Crevice Tool



*ProLevel Filtration® System w/HEPA Media

captures 97.44% at 0.3-.5 microns per ASTM F3150

ProLevel Filtration System w/ HEPA Media includes:

1. Snap Lock Intercept Micro® Filter
2. Motor Intake Filter
3. 2 Post Motor Replaceable Filters made from HEPA Media.

*The filtration value of ProTeam's ProLevel Filtration® System in this vacuum is achieved by the use of a multi-stage filtration system, including intercept micro filter, foam filter, and post-motor filter made from HEPA media, as tested per ASTM F3150.

Exceeds industry regulation testing standards set by the Carpet and Rug Institute and the requirements of the US Green Building Council's LEED rating system on performance and filtration.

Certification

This product is UL Listed and has been evaluated to appropriate US and Canadian safety standards.